



Representative

**Catalog Number:** 7360  
**Product ID:** 7TAD012330R0024  
**UPC Number:** 78621007360  
**EAN Number:** 05414363076032  
**Status:** A

5/16 Inch Steel Insulated Liquidtight Connector With PG Thread and Chromate Finish, Thread Size 9

- Quick and easy to install by hand, no special tool needed.
- Provides a positive seal against oil, liquids, moisture and dust

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Liquidtight Flexible Metal Conduit Fittings
Special Features	CSA Certified Dusttight and Watertight. UL Listed Liquidtight.
Application	Nylon Insulated Straight Fittings
Size	5/16 Inch
Material	Nylon Insulated

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	5/16 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	Other
Thread connection size	PG9
One-piece	N
Material housing	Steel
Thread length	12mm
Total length	36mm
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UL	N

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	100
Outer Dimensions (inches)	10.8x9.7x3.5
Weight Uom	44.13 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website
Instruction Sheet	TA00210-TB2

### Header

3D Model	Available on Website
----------	----------------------

