



Representative

Catalog Number: 7363
Product ID: 7TAD012320R0000
UPC Number: 78621007363
EAN Number: 05414363076063
Status: A

1/2 Inch Steel Insulated Liquidtight Connector With PG Thread and Chromate Finish, Thread Size 16

- Quick and easy to install by hand, no special tool needed.

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-PG Metric Thread
Application	Provides a positive seal against oil, liquids, moisture and dust.
Standard	UL E23018, CSA
Size	1/2 Inch
Material	Steel
Finish	Galvanized

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	Other
Thread connection size	PG16
One-piece	N
Material housing	Steel
Thread length	14mm
Total length	41mm
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	25
Inner Dimensions (inches)	6.25x4.75x3.25
Outer Quantity	100
Outer Dimensions (inches)	9.8x9.1x7.1
Weight Uom	17.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Instruction Sheet	TA00210-TB2
Support/Tools	Available on Website
Marketing Brochure	Available on Website
Catalog US	Available on Website

Header

3D Model	Available on Website
----------	----------------------

