



 PRODUCT-DETAILS

2920

1/2 IN RANGER CORD CONN .125-.375



General Information

| | |
|-------------------------------|--|
| Extended Product Type: | 2920 |
| Product ID: | 7TBD105170R0000 |
| EAN: | 5414363101703 |
| Catalog Description: | 1/2 IN RANGER CORD CONN .125-.375 |
| Long Description: | Liquidtight Strain Relief Connector, 1/2 Inch, Straight, Cord Range 0.125 to 0.375 Inch, Throat Diameter 9/16 Inch, Steel Body, Glandnut, and Grip, Rubber Bushing |
| Display Name: | 2920 |

Additional Information

| | |
|----------------------|--|
| Application: | A Liquidtight Fitting to Secure Flexible Cord or Power Cable to a Box or Enclosure and Provide Strain Relief |
| Product Type: | Cord Connectors-Straight |

Ordering

| | |
|-------------|---------------|
| EAN: | 5414363101703 |
|-------------|---------------|

UPC: 786210029207

Technical

| | |
|----------------------|----------|
| Number of Batteries: | 0 |
| Color: | Metallic |
| Material: | Steel |
| Size: | 1/2 Inch |

Environmental

| | |
|----------------|---------------------------|
| WEEE Category: | Product Not in WEEE Scope |
|----------------|---------------------------|

Container Information

| | |
|---------------------------------|------------------|
| Package Level 1 Units: | 25 piece |
| Package Level 1 Height: | 3 in 76 mm |
| Package Level 1 Depth / Length: | 5 in 127 mm |
| Package Level 1 Width: | 4.5 in 114 mm |

External Classifications and Standards

| | |
|---------|------------------------|
| ETIM 8: | EC000441 - Cable gland |
| ETIM 9: | EC000441 - Cable gland |
| UNSPSC: | 39121431 |

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems > T&B Cord and Cable Fittings

