



Representative

Catalog Number: 8130
Product ID: 7TAD013170R0028
UPC Number: 78621008130
EAN Number: 05414363146414
Status: A

1/2 Inch Threadless Short Elbow, Malleable Iron and Nylon Insulated for Use with Rigid/IMC Conduit

- Eliminates need to thread conduit. As with straight couplings, this connector makes a concrete-tight connection.

North American Specifications (UNSPSC)

UNSPSC	39131717 Electrical conduit elbow
IGCC	5746 Electrical conduit elbow
Type	Rigid/IMC Conduit Fittings
Special Features	Ideal for Entering Enclosure or Conduit Body At Right Angles
Application	To Connect and Effectively Bond Threaded Rigid Metal Conduit/Intermediate Metal Conduit to a Box or Enclosure, or to Couple Ends of Threaded Conduit
Standard	UL E23018, CSA
Material	Malleable Iron
Trade Size	1/2 in

European Specifications (ETIM)

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Other
Colour	Natural colour
Model	Rigid
Angle of bow	90°

Packaging

Inner Quantity	10
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	20
Outer Dimensions (inches)	6.8x5.3x5.7
Weight Uom	30.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------