



Representative

Catalog Number: 8223
Product ID: 7TAD013160R0025
UPC Number: 78621008223
EAN Number: 05414363146469
Status: A

3/4 Inch Threadless Connector, Malleable Iron with Nylon Insulator for Use with Rigid/IMC Conduit

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Type	Threadless Connector
Application	To Connect and Effectively Bond Threadless Rigid Metal Conduit/Intermediate Metal Conduit to a Box or Enclosure, or to Couple Ends of Threadless Conduit
Standard	UL E23018, CSA
Size	3/4 Inch
Material	Malleable Iron

European Specifications (ETIM)

ETIM	EC001492 Coupler for cable protection tube
Material	Metal
Material quality	Other
Surface protection	Untreated
Colour	Natural colour
Outer diameter	44.45mm

Packaging

Inner Quantity	10
Inner Dimensions (inches)	6x4.5x3
Outer Quantity	20
Outer Dimensions (inches)	9.1x5.5x7
Weight Uom	27.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------