




Actual



Representative

Catalog Number: 848AL
Product ID: 7TAD013140R0005
UPC Number: 78621080170
Status: A

2-1/2 Inch Chase Nipple, Aluminum, Electro Zinc Plated for Use with Rigid/IMC Conduit

North American Specifications (UNSPSC)

UNSPSC	39131718 Electrical conduit nipple
IGCC	5753 Electrical conduit nipple
Type	Chase Conduit Nipple
Application	To Effectively Bush Factory or Field-Punched, Cut, or Drilled Holes In Metal Boxes or Enclosures. To Couple Boxes Back-to-Back
Standard	UL E23018, CSA
Material	Aluminum
Finish	Electro Zinc Plated
Trade Size	2-1/2 in

European Specifications (ETIM)

ETIM	EC001469 Protective hose adapter
With outer thread	Y
Thread size outer thread metric	63
Material housing	Aluminium
Material quality	Other
Surface protection	Untreated
Model	Straight
Material sealing	No sealing

Packaging

Inner Quantity	5
Inner Dimensions (inches)	6x5x4
Outer Quantity	20
Outer Dimensions (inches)	13.4x5.1x10.9
Weight Uom	20.75 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------