




Actual



Representative

Catalog Number: 850
Product ID: 7TAD013140R0006
UPC Number: 78621000850
EAN Number: 05414363076766
Status: A

3-1/2 Inch Chase Nipple, Malleable Iron for Use with Rigid/IMC Conduit

North American Specifications (UNSPSC)

UNSPSC	39131718 Electrical conduit nipple
IGCC	5753 Electrical conduit nipple
Type	Chase Conduit Nipple
Application	To Effectively Bush Factory or Field-Punched, Cut, or Drilled Holes In Metal Boxes or Enclosures. To Couple Boxes Back-to-Back
Standard	UL E23018, CSA
Material	Malleable Iron
Trade Size	3-1/2 in

European Specifications (ETIM)

ETIM	EC001469 Protective hose adapter
With outer thread	Y
Thread size outer thread metric	91
Material housing	Other
Material quality	Other
Surface protection	Untreated
Model	Straight
Material sealing	No sealing

Packaging

Inner Quantity	1
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	5
Outer Dimensions (inches)	16.4x5x5.5
Weight Uom	171 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001846
Catalog Page	Available on Website

Header

3D Model	Available on Website
----------	----------------------