



Representative

**Catalog Number:** 8625  
**Product ID:** 7TAD013160R0036  
**UPC Number:** 78621008625  
**EAN Number:** 05414363146742  
**Status:** Active

2 Inch Set Screw Connector, Steel with Nylon Insulated Throat for Use with Rigid/IMC Conduit

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	T&B
Type	Set Screw Connector
Application	To Connect and Effectively Bond Threadless Rigid Metal Conduit/Intermediate Metal Conduit to a Box or Enclosure, or to Couple Ends of Threadless Conduit
Standard	UL E23018, CSA
Size	2 Inch
Material	Steel
Finish	Electro Zinc Plated

### European Specifications (ETIM)

ETIM	EC001492 Coupler for cable protection tube
Material	Metal
Material quality	Other
Surface protection	Untreated
Colour	Natural colour
Outer diameter	82.55mm

### Packaging

Inner Quantity	2
Inner Dimensions (inches)	6.3x3.2x4.69
Outer Quantity	20
Outer Dimensions (inches)	21.6x9.9x6.9
Weight Uom	109.75 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

### Header

3D Model	Available on Website
----------	----------------------