



Actual



Representative

**Catalog Number:** 8720  
**Product ID:** 7TAD013170R0045  
**UPC Number:** 78621008720  
**EAN Number:** 05414363146766  
**Status:** A

2-1/2 Inch Coupling, Malleable Iron for Use with Threadless Rigid/IMC Conduit

- Tightened with a wrench they make a U.L. Listed and CSA Certified concrete-tight connection.
- To Connect Threaded Metal Conduit to a Threadless Opening in a Box or Enclosure

### North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Type	Compression Couplings & Connectors
Special Features	Eliminate Conduit Threading.
Application	To Couple and Effectively Bond Threaded Ends of Rigid Metal Conduit/Intermediate Conduit Where Neither Length of Conduit Can Be Roated
Standard	UL E23018, CSA
Trade Size	2-1/2 in
Material	Malleable Iron

### European Specifications (ETIM)

ETIM	EC000939 Coupler for installation tubes
Material	Metal
Material quality	Other
Model	Thread
Two piece	N
With inspection opening and cover	N

### Packaging

Outer Quantity	5
Outer Dimensions (inches)	13.3x4.7x10.9
Weight Uom	5.06 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website

### Header

3D Model	Available on Website
----------	----------------------