



Actual



Representative

**Catalog Number:** 8850  
**Product ID:** 7TAD013170R0051  
**UPC Number:** 78621008850  
**EAN Number:** 05414363183181  
**Status:** A

3-1/2 Inch Coupling, Malleable Iron for Use with Threadless Rigid/IMC Conduit

- Tightened with a wrench they make a U.L. Listed and CSA Certified concrete-tight connection.
- To Connect Threaded Metal Conduit to a Threadless Opening in a Box or Enclosure

**North American Specifications (UNSPSC)**

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Type	Compression Couplings & Connectors
Special Features	Eliminate Conduit Threading.
Application	To Couple and Effectively Bond Threaded Ends of Rigid Metal Conduit/Intermediate Conduit Where Neither Length of Conduit Can Be Roated
Standard	UL E23018, CSA
Trade Size	3-1/2 in
Material	Malleable Iron

**European Specifications (ETIM)**

ETIM	EC000939 Coupler for installation tubes
Material	Metal
Material quality	Other
Model	Thread
Two piece	N
With inspection opening and cover	N

**Packaging**

Outer Quantity	1
Outer Dimensions (inches)	6.5x5.3x4.69
Weight Uom	6.8 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

**Header**

3D Model	Available on Website
----------	----------------------