



Actual

Catalog Number: BCG-0752
Product ID: 7TCA303030R0059
UPC Number: 78621015695
EAN Number: 05415022427998
Status: Active

Non Armoured Cable Gland, Thread Size 3/4 Inch NPT, Cable Range 13 to 18 Millimeters, Thread Length 13 Millimeters, Nickel Plated Brass

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Non Armoured Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	cULus, RoHS, WEEE, LVD
Size	3/4 Inch NPT
Conductor Range	13 to 18 Millimeters
Material	Brass
Finish	Nickel plated
Color	Metallic
NEMA Rating	NEMA 4
Temperature Rating	-20 to +100 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Thread length	13mm
Suitable for cable diameter	13 - 18mm
Material	Metal
Material quality	Brass
Surface protection	Nickel-plated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-20-+100°C

Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	30
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.02 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000028
Technical Drawing / Data Sheet Canada	TDS000028
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website

Thomas & Betts - USA