



Actual



Representative

Catalog Number: BGA200-14-20
Product ID: 7TAD013050R0019
UPC Number: 78621016297
Status: A

2 Inch Blackjack Grounding Bushing, Aluminum, Galvanized, Wire Range 14 to 2/0 for Use with Threaded or Threadless Rigid/IMC Conduit

North American Specifications (UNSPSC)

| | |
|-------------|----------------------------------|
| UNSPSC | 39121312 Electrical bushing |
| IGCC | 4442 Electrical bushing |
| Type | Grounding Bushings & Accessories |
| Application | For Use with Rigid/IMC Conduit |
| Standard | UL E3060, CSA |
| Size | 2 Inch |
| Material | Aluminum |

European Specifications (ETIM)

| | |
|----------------|----------------------------|
| ETIM | EC002357 Support insulator |
| Length | 17.68mm |
| Outer diameter | 71.88mm |

Packaging

| | |
|---------------------------|-------------------|
| Inner Quantity | 5 |
| Inner Dimensions (inches) | 6x4.5x3 |
| Outer Quantity | 25 |
| Outer Dimensions (inches) | 15.9x8.6x7.7 |
| Weight Uom | 16.5 lbs. per 100 |

Documents / Support Tools

| | |
|-----------------------------------|----------------------|
| Technical Drawing / Data Sheet US | Available on Website |
|-----------------------------------|----------------------|

Header

| | |
|----------|----------------------|
| 3D Model | Available on Website |
|----------|----------------------|