



Actual



Family

Catalog Number: CC-PG21-G
Product ID: 7TAD105080R0020
UPC Number: 78621021166
EAN Number: 05415022257311
Status: A
Replacement Catalog: NCG-PG211LG

Cable Gland with PG Threads, Thread Size PG21, Cord Range 0.512 Inch/13mm to 0.709 Inch/18mm, Thread Length 0.433 Inch/11mm, IP68 Rating, Halogen Free, Nylon, Gray

- Sturdy cable sealing mechanism which results in superior strain relief.
- Compact size ensures quick and easy installation in cramped spaces
- Non-metallic construction provides excellent corrosion, chemical and impact resistance.

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Cable Glands
Special Features	Sturdy Cable Sealing Mechanism Which Results In Superior Strain Relief
Application	Ideal for Connections and Strain Relief in Cramped Spaces
Standard	UL E13938, CSA
Size	PG21
Conductor Range	0.512 Inch/13mm to 0.709 Inch/18mm
Material	Nylon
Color	Gray
NEMA Rating	4
Temperature Rating	-30 to +80 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	PG
Nominal thread size metric/PG	21
Thread length	11.0mm
Suitable for cable diameter	13.0-18.0mm
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP68
Colour	Light grey
Model	Straight
Operating temperature	-30-+80°C

Packaging

Inner Quantity	10
Inner Dimensions (inches)	6x4.5x3
Outer Quantity	50
Outer Dimensions (inches)	21.7x5.4x6.9
Weight Uom	3.38 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000004
Instruction Sheet	TA02021-TB2

Header

3D Model	Available on Website
----------	----------------------

