



Actual



Family

**Catalog Number:** CC-PG9-G  
**Product ID:** 7TAD105080R0025  
**UPC Number:** 78621021162  
**EAN Number:** 05415022384581  
**Status:** A  
**Replacement Catalog:** NCG-PG91LG

Cable Gland with PG Threads, Thread Size PG9, Cord Range 0.157 Inch/4mm to 0.315 Inch/8mm, Thread Length 0.315 Inch/8mm, IP68 Rating, Halogen Free, Nylon, Gray

- Sturdy cable sealing mechanism which results in superior strain relief.
- Compact size ensures quick and easy installation in cramped spaces
- Non-metallic construction provides excellent corrosion, chemical and impact resistance.

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Cable Glands
Special Features	Sturdy Cable Sealing Mechanism Which Results In Superior Strain Relief
Application	Ideal for Connections and Strain Relief in Cramped Spaces
Standard	UL E13938, CSA
Size	PG9
Conductor Range	0.157 Inch/4mm to 0.315 Inch/8mm
Material	Nylon
Color	Gray
NEMA Rating	4
Temperature Rating	-30 to +80 C

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	PG
Nominal thread size metric/PG	9
Thread length	8.0mm
Suitable for cable diameter	4.0-8.0mm
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP68
Colour	Light grey
Model	Straight
Operating temperature	-30-+80°C

### Packaging

Inner Quantity	50
Inner Dimensions (inches)	6x4.5x3
Outer Quantity	200
Outer Dimensions (inches)	10x9.25x8.5
Weight Uom	1.5 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000004
Instruction Sheet	TA02021-TB2

### Header

3D Model	Available on Website
----------	----------------------

