



Location: city of phoenix

city of phoenix

2470 s 22nd ave



Representative

Catalog Number: CLGES01G-L
Product ID: 7TAA012CA0R0017
UPC Number: 78621015092
EAN Number: 05415022445855
Status: A

Liquid Tight Flexible Metallic Conduit, General Purpose, Galvanized Steel with PVC Jacket, Conduit Size 3/8 Inch, Length 300 Meters/1,000 Feet, Working Temperature -20 to 80 Degrees C, Compliant to RoHS, Gray

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Flexible Metal Conduit
Standard	RoHS
Trade Size	3/8 in
Outside Diameter	0.710 in
Inside Diameter	0.484 in
Length	1,000 ft
Material	Galvanized Steel with PVC Jacket
Color	Gray

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	16mm
Nominal size in inch	3/8 inch
Outer diameter	18.03mm
Inner diameter	12.29mm
Material	Steel
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+80°C
Colour	Grey
With approval according to UL	N
Approved according to CSA	N

Packaging

Outer Quantity	1000
Outer Dimensions (inches)	20x30x30
Weight Uom	0.2 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000016
--------------------------------	-----------