

**Catalog Number:** CLGES02G-K  
**Product ID:** 7TAA012CA0R0011  
**UPC Number:** 78621015086  
**EAN Number:** 05415022445794  
**Status:** Active



Liquid Tight Flexible Metallic Conduit, General Purpose, Galvanized Steel with PVC Jacket, Conduit Size 1/2 Inch, Length 150 Meters/500 Feet, Working Temperature -20 to 80 Degrees C, Compliant to RoHS, Gray

Representative

### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	T&B
Type	Flexible Metal Conduit
Standard	RoHS
Trade Size	1/2 Inch
Outside Diameter	0.840 Inches
Inside Diameter	0.622 Inches
Length	500 ft
Material	Galvanized Steel with PVC Jacket
Color	Gray

### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	20mm
Nominal size in inch	1/2 inch
Outer diameter	21.33mm
Inner diameter	15.80mm
Material	Steel
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+80°C
Colour	Grey
With approval according to UL	N
Approved according to CSA	N

### Packaging

Outer Quantity	500
Outer Dimensions (inches)	20x24x24
Weight Uom	0.24 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000016
--------------------------------	-----------