



Catalog Number: CLGES04G-C
Product ID: 7TAA012CA0R0003
UPC Number: 78621015078
EAN Number: 05415022445718
Status: A



Liquid Tight Flexible Metallic Conduit, General Purpose, Galvanized Steel with PVC Jacket, Conduit Size 1 Inch, Length 30 Meters/100 Feet, Working Temperature -20 to 80 Degrees C, Compliant to RoHS, Gray

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Flexible Metal Conduit
Standard	RoHS
Trade Size	1 in
Outside Diameter	1.315 in
Inside Diameter	1.041 in
Length	100 ft
Material	Galvanized Steel with PVC Jacket
Color	Gray

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	32mm
Nominal size in inch	1 inch
Outer diameter	33.40mm
Inner diameter	26.44mm
Material	Steel
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+80°C
Colour	Grey
With approval according to UL	N
Approved according to CSA	N

Packaging

Outer Quantity	100
Outer Dimensions (inches)	25.25x24.5x8.25
Weight Uom	0.43 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000016
--------------------------------	-----------