



**Catalog Number:** CLGES04G-J  
**Product ID:** 7TAA012CA0R0013  
**UPC Number:** 78621015088  
**EAN Number:** 05415022445817  
**Status:** A



Liquid Tight Flexible Metallic Conduit, General Purpose, Galvanized Steel with PVC Jacket, Conduit Size 1 Inch, Length 120 Meters/400 Feet, Working Temperature -20 to 80 Degrees C, Compliant to RoHS, Gray

Representative

**North American Specifications (UNSPSC)**

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Flexible Metal Conduit
Standard	RoHS
Trade Size	1 in
Outside Diameter	1.315 in
Inside Diameter	1.041 in
Length	400 ft
Material	Galvanized Steel with PVC Jacket
Color	Gray

**European Specifications (ETIM)**

ETIM	EC001179 Protective metallic hose
Nominal diameter	32mm
Nominal size in inch	1 inch
Outer diameter	33.40mm
Inner diameter	26.44mm
Material	Steel
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+80°C
Colour	Grey
With approval according to UL	N
Approved according to CSA	N

**Packaging**

Outer Quantity	400
Outer Dimensions (inches)	20x30x30
Weight Uom	0.43 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000016
--------------------------------	-----------