



**Catalog Number:** CLGES08G-A  
**Product ID:** 7TAA012CA0R0007  
**UPC Number:** 78621015082  
**EAN Number:** 05415022445756  
**Status:** A



Liquid Tight Flexible Metallic Conduit, General Purpose, Galvanized Steel with PVC Jacket, Conduit Size 2-1/2 Inch, Length 8 Meters/25 Feet, Working Temperature -20 to 80 Degrees C, Compliant to RoHS, Gray

Representative

**North American Specifications (UNSPSC)**

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Flexible Metal Conduit
Standard	RoHS
Trade Size	2-1/2 in
Outside Diameter	2.875 in
Inside Diameter	2.480 in
Length	25 ft
Material	Galvanized Steel with PVC Jacket
Color	Gray

**European Specifications (ETIM)**

ETIM	EC001179 Protective metallic hose
Nominal diameter	70mm
Nominal size in inch	2 1/2 inch
Outer diameter	73.03mm
Inner diameter	62.99mm
Material	Steel
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+80°C
Colour	Grey
With approval according to UL	N
Approved according to CSA	N

**Packaging**

Outer Quantity	25
Outer Dimensions (inches)	33.62x37x10.38
Weight Uom	1.92 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000016
--------------------------------	-----------