

**Catalog Number:** CLGES09G-A  
**Product ID:** 7TAA012CA0R0008  
**UPC Number:** 78621015083  
**EAN Number:** 05415022445763  
**Status:** Active



Liquid Tight Flexible Metallic Conduit, General Purpose, Galvanized Steel with PVC Jacket, Conduit Size 3 Inch, Length 8 Meters/25 Feet, Working Temperature -20 to 80 Degrees C, Compliant to RoHS, Gray

Representative

### North American Specifications (UNSPSC)

|                  |                                  |
|------------------|----------------------------------|
| UNSPSC           | 39131706 Electrical conduit      |
| IGCC             | 5543 Liquid Tight Conduit        |
| Brand Name       | T&B                              |
| Type             | Flexible Metal Conduit           |
| Standard         | RoHS                             |
| Trade Size       | 3 Inch                           |
| Outside Diameter | 3.500 Inches                     |
| Inside Diameter  | 3.070 Inches                     |
| Length           | 25 ft                            |
| Material         | Galvanized Steel with PVC Jacket |
| Color            | Gray                             |

### European Specifications (ETIM)

|   |                                   |
|---|-----------------------------------|
| ETIM                                      | EC001179 Protective metallic hose |
| Nominal diameter                          | 80mm                              |
| Nominal size in inch                      | 3 inch                            |
| Outer diameter                            | 88.90mm                           |
| Inner diameter                            | 77.98mm                           |
| Material                                  | Steel                             |
| Sheathing material 2nd coating (exterior) | PVC                               |
| Operating temperature                     | -20-+80°C                         |
| Colour                                    | Grey                              |
| With approval according to UL             | N                                 |
| Approved according to CSA                 | N                                 |

### Packaging

|                           |                |
|---------------------------|----------------|
| Outer Quantity            | 25             |
| Outer Dimensions (inches) | 8.5x50x50      |
| Weight Uom                | 2.52 lbs. Each |

### Documents / Support Tools

|                                       |           |
|---------------------------------------|-----------|
| Technical Drawing / Data Sheet        | TDS000016 |
| Technical Drawing / Data Sheet Canada | TDS000016 |