

Catalog Number: CMACS11M-A
Product ID: 7TAA012CE0R0010
UPC Number: 78621015150
EAN Number: 05415022445190
Status: Active



Flexible Metallic Conduit, Heavy Gauge Aluminum Alloy, Conduit Size 4 Inch, Length 8 Meters/25 Feet, UL, CSA, Compliant to RoHS, Metallic

Actual

North American Specifications (UNSPSC)

| | |
|------------------|-----------------------------|
| UNSPSC | 39131706 Electrical conduit |
| IGCC | 5535 Electrical conduit |
| Brand Name | T&B |
| Type | Flexible Metallic Conduit |
| Standard | UL, CSA, RoHS |
| Trade Size | 4 Inches |
| Outside Diameter | 4.560 Inches |
| Inside Diameter | 4.000 Inches |
| Length | 25 ft |
| Material | Heavy Gauge Aluminum |
| Color | Metallic |

European Specifications (ETIM)

| | |
|---|-----------------------------------|
| ETIM | EC001179 Protective metallic hose |
| Nominal diameter | 100mm |
| Nominal size in inch | 4 inch |
| Outer diameter | 115.82mm |
| Inner diameter | 101.6mm |
| Material | Aluminium |
| Sheathing material 2nd coating (exterior) | Not sheathed |
| Colour | Metallic |
| With approval according to UL | Y |
| Approved according to CSA | Y |

Packaging

| | |
|---------------------------|-----------------|
| Outer Quantity | 25 |
| Outer Dimensions (inches) | 6.5x60.25x60.25 |
| Weight Uom | 1.42 lbs. Each |

Documents / Support Tools

| | |
|---------------------------------------|-----------|
| Technical Drawing / Data Sheet | TDS000020 |
| Technical Drawing / Data Sheet Canada | TDS000020 |