



Family

**Catalog Number:** COND2SS  
**Product ID:** 7TAD013020R0008  
**UPC Number:** 78620999315  
**Status:** A

2 Inch Type 304 Stainless Steel Conduit with Type 304 Stainless Steel Coupling

- Exceeds requirements for wash down applications
- Also available in marine grade-Type 316 stainless steel
- Each 10 foot length of conduit ships with one Type 316 stainless steel conduit coupling
- Type 316 stainless steel couplings are sold separately
- Type 304 stainless steel offers up to five times the lifespan when compared to standard galvanized steel conduit in corrosive environments
- Water and wastewater treatment
- Food and beverage processing
- Marine and coastal facilities
- Pharmaceutical manufacturing
- Pulp and paper processing
- Corrosive environments
- Meets stringent sanitary requirements

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Type	Rigid/IMC Conduit Fittings
Special Features	Standard NPT Threads for Easy Installation
Application	Petrochemical Refining and Processing
Trade Size	2 in
Outside Diameter	2.375 in
Inside Diameter	2.067 in
Material	304 Stainless Steel
Color	Metallic

#### Packaging

Inner Quantity	10
Outer Quantity	200
Outer Dimensions (inches)	126x14.75x14
Weight Uom	340.5 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001049
--------------------------------	------------