



Family

Catalog Number: COND2SST
Product ID: 7TAD013020R0009
UPC Number: 78620999323
Status: A

2 Inch Type 316 Stainless Steel Conduit with Type 316 Stainless Steel Coupling

- Exceeds requirements for wash down applications
- Also available in Type 304 stainless steel
- Each 10 foot length of conduit ships with one Type 316 stainless steel conduit coupling
- Type 316 stainless steel couplings are sold separately
- Type 316 stainless steel offers up to eight times the lifespan when compared to standard galvanized steel conduit in corrosive environments
- Water and wastewater treatment
- Food and beverage processing
- Marine and coastal facilities
- Pharmaceutical manufacturing
- Pulp and paper processing
- Corrosive environments
- Meets stringent sanitary requirements

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Type	Rigid/IMC Conduit Fittings
Special Features	Standard NPT Threads for Easy Installation
Application	Petrochemical Refining and Processing
Trade Size	2 in
Outside Diameter	2.375 in
Inside Diameter	2.067 in
Material	316 Stainless Steel
Color	Metallic

Packaging

Outer Quantity	200
Outer Dimensions (inches)	126x14.75x14
Weight Uom	3.71 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001049
Catalog Page	Available on Website