



Catalog Number: CPO-A-1500-48
Product ID: 7TAA017320R0010
UPC Number: 78621025299
Status: A



Thin-Wall Heat Shrinkable Tubing, Black Polyolefin, 1-1/2 Inch, Shrink Ratio 3:1, Length 48 Inches, Operating Temperature -55 to 110 Degrees Celsius, Adhesive Lined

- Adhesive lined for moisture-proof environmental seal.
- High 3:1 shrink ratio for covering irregularly shaped objects.

Actual

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Thin-Wall Heat Shrinkable Tubing
Special Features	Adhesive lined for moisture-proof environmental seal.
Shrink Ratio	3:1
Thickness	Thin
Length	48 in
Color	Black

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	3:1
Inner diameter before heat-shrink	38mm
Inner diameter after heat-shrink	12.954mm
Nominal diameter inch	1 1/2 inch
Wall thickness after shrinking	1.016mm
Length	1.22m
Operation temperature	-55-+110°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	Y
Printable	N
UL approval	N

Packaging

Outer Quantity	25
Outer Dimensions (inches)	8.375x49x10.875
Weight Uom	39 lbs. per 100

Documents / Support Tools

Safety Data Sheet (SDS) Global	SDS-00046-TB2
Catalog	Available on Website