



Actual

## Project: Inquiry

<b>Catalog Number:</b>	<b>DX-5</b>
<b>Product ID:</b>	7TAH007070R0070
<b>UPC Number:</b>	78378615001
<b>EAN Number:</b>	05414363150336
<b>Status:</b>	A

Duct Seal Compound, (5) 1 pound packages. To Seal openings from air, dust or water around EMT or rigid conduit raceway. Not to be used for electrical insulation applications.

- Can be painted immediately after application.
- No unpleasant order.
- Contains no asbestos.
- Workable temperature range - +20 degree F to 212 degree F.
- Service temperature range; -40 degree F to 250 degree F.

### North American Specifications (UNSPSC)

UNSPSC	39131608 Duct sealing system
IGCC	5401 Duct sealing system
Type	Chemical Products
Special Features	Can be painted immediately after application.
Application	Workable temperature range - +20 degree F to 212 degree F.
Size	5 Pound
Temperature Rating	-40 to 250 F

### European Specifications (ETIM)

ETIM	EC002722 Jointing compound
Colour	Grey
Packaging	Other

### Packaging

Inner Quantity	1
Outer Quantity	10
Outer Dimensions (inches)	12.5x12.5x9.2
Weight Uom	532.55 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Safety Data Sheet (SDS) Global	SDS-00032-TB2