

Catalog Number: EFC025
Product ID: 7TAD012740R0000
UPC Number: 78621070111
EAN Number: 05414363100294
Status: A



Actual

1/4 Inch Black Corrugated PVC Flexible Tubing

- Extremely fast installation
- Liquidtight with specified fittings.
- Good tensile strength provides excellent pullout protection and smooth inner diameter allows easy wire pulling.

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Type	Type B Liquidtight Tubing & Fittings
Special Features	Maximum Flexibility In Tight Applications.
Application	Protection of Fiber Optic Cable, Installation of Instrumentation and Control Cable, Indoor and Outdoor Lighting, Packaging Equipment, Marine and Shipboard Wiring, and Flexing-Component Wiring Protection on Robots, Graphic Arts Equipments, Etc.
Standard	UL E96548
Trade Size	1/4 in
Material	PVC
Color	Black

European Specifications (ETIM)

ETIM	EC001175 Corrugated plastic hose
Nominal size in inch	1/4 inch
Material	PVC
Operating temperature	-18-+60°C
Oil resistant	Y
Colour	Black
Lengthwise slotted	N
Closable (two-part)	N

Packaging

Outer Quantity	100
Outer Dimensions (inches)	19.9x19.6x5.8
Weight Uom	7.56 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------