



**Catalog Number:** EFC038-2  
**Product ID:** 7TAD012980R0187  
**UPC Number:** 78621070088  
**Status:** A



Representative

3/8 Inch Blue Corrugated PVC Flexible Tubing for Use With Bullet, Liquidtight Fittings.

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Type	Flexible Tubing
Special Features	Maximum Flexibility In Tight Applications.
Application	Protection of Fiber Optic Cable, Installation of Instrumentation and Control Cable, Indoor and Outdoor Lighting, Packaging Equipment, Marine and Shipboard Wiring, and Flexing-Component Wiring Protection on Robots, Graphic Arts Equipments, Etc.
Standard	UL E96548
Trade Size	3/8 in
Material	PVC
Color	Blue

#### European Specifications (ETIM)

ETIM	EC001175 Corrugated plastic hose
Nominal size in inch	3/8 inch
Material	PVC
Operating temperature	-18-+60°C
Oil resistant	Y
Colour	Blue
Lengthwise slotted	N
Closable (two-part)	N

#### Packaging

Outer Quantity	100
Outer Dimensions (inches)	19.5x19.5x5.5
Weight Uom	7 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------