



**Catalog Number:** ELL1/245SS  
**Product ID:** 7TAD013020R0024  
**UPC Number:** 78621008440  
**Status:** A



Representative

1/2 Inch Rigid Elbow, 45 Degree Bend, for Use with Rigid/IMC Conduit, 304 Stainless Steel

#### North American Specifications (UNSPSC)

UNSPSC	39131717 Electrical conduit elbow
IGCC	5746 Electrical conduit elbow
Type	Rigid and Intermediate Metal Conduit Fittings
Special Features	Pressure-Sealing Sleeves Protect Connections
Application	Installed at End of Conduit Runs, in a Box or a Fitting Hub to Change Direction in Threaded Rigid Conduit
Material	304 Stainless Steel
Trade Size	1/2 in

#### European Specifications (ETIM)

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Stainless steel V2A
Colour	Natural colour
Model	Rigid
Angle of bow	45°

#### Packaging

Outer Quantity	25
Outer Dimensions (inches)	4.52x4.72x12.4
Weight Uom	0.4 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001606
--------------------------------	------------