



**Catalog Number:** ELL3/4SS  
**Product ID:** 7TAD013020R0019  
**UPC Number:** 78621008433  
**Status:** A



Representative

3/4 Inch Rigid Elbow, 90 Degree Bend, for Use with Rigid/IMC Conduit, 304 Stainless Steel

#### North American Specifications (UNSPSC)

UNSPSC	39131717 Electrical conduit elbow
IGCC	5746 Electrical conduit elbow
Type	Rigid and Intermediate Metal Conduit Fittings
Special Features	Pressure-Sealing Sleeves Protect Connections
Application	Installed at End of Conduit Runs, in a Box or a Fitting Hub to Change Direction in Threaded Rigid Conduit
Material	304 Stainless Steel
Trade Size	3/4 in

#### European Specifications (ETIM)

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Stainless steel V2A
Colour	Natural colour
Model	Rigid
Angle of bow	90°

#### Packaging

Outer Quantity	25
Outer Dimensions (inches)	10.23x5.9x8.66
Weight Uom	0.96 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001606
--------------------------------	------------