



Actual

Catalog Number: EX-M50
Product ID: 7TCA297140R0017
UPC Number: 78621019183
EAN Number: 05011949018594
Status: Active

Stopping Plug, M50 Thread, Suitable for Use in Zones 1, 2 , 21, and 22, Exe I, Exe II, and Extd IIIC, IP66-68 Rating, Flame Retardant Polyamide (Nylon 6), Black

North American Specifications (UNSPSC)

UNSPSC	39121404 Electrical sleeves
IGCC	4529 Cable end sleeve
Brand Name	Kopex
Type	Conduit Stopping Plug
Application	Provide Protection for the End of Conduit Systems
Standard	ATEX :- Baseefa 08ATEX0324, IECEx :- IECEx BAS08.0109
Insulation	IP66-68
Material	Flame Retardant Polyamide/Nylon 6
Color	Black
Connection	Straight, Screw In
Size	M50 Thread

European Specifications (ETIM)

ETIM	EC000032 Plug for cable screw gland
Thread type	Metric
Nominal thread size metric/PG	50
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
Colour	Black
For Ex-zone gas	1, 2
For Ex-Zone dust	21, 22

Packaging

Inner Quantity	5
Outer Quantity	10
Outer Dimensions (inches)	1x1x1
Weight Uom	0.02 lbs. Each