



Actual

Catalog Number: EXN/M25/SP
Product ID: 7TCA297140R0098
UPC Number: 78621019084
EAN Number: 05011949014268
Status: Active

Stopping Plug, M25 Thread, Suitable for Use in Zones 1, 2, 21, and 22, Exd I and Exd IIC, UL1203, Nickel Plated Brass

North American Specifications (UNSPSC)

UNSPSC	39121404 Electrical sleeves
IGCC	4529 Cable end sleeve
Brand Name	Kopex
Type	Conduit Stopping Plug
Application	Provide Protection for the End of Conduit Systems
Standard	UL1203, ATEX :- Baseefa 08ATEX0324, IECEx :- IECEx BAS08.0109
Material	Nickel Plated Brass
Color	Metallic
Connection	Straight, Screw In
Size	M25 Thread

European Specifications (ETIM)

ETIM	EC000032 Plug for cable screw gland
Thread type	Metric
Nominal thread size metric/PG	25
Material	Metal
Material quality	Brass
Surface protection	Nickel-plated
Colour	Natural colour
For Ex-zone gas	1, 2
For Ex-Zone dust	21, 22

Packaging

Outer Quantity	10
Outer Dimensions (inches)	1x1x1
Weight Uom	0.15 lbs. Each

Header

3D Model	Available on Website
----------	----------------------