



Actual

**Catalog Number:** EXN/M50-075/TC  
**Product ID:** 7TCA297130R0300  
**UPC Number:** 78621018930  
**EAN Number:** 05011949011489  
**Status:** Active

Adapter, Thread Converter, M50 Male Thread to 3/4 Inch NPT Female Thread, Suitable for Use in Zones 1, 2, 21, and 22, Ex e and Ex d, UL1203, Nickel Plated Brass

### North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Brand Name	Kopex
Type	Conduit Thread Converter
Application	Suitable for use in Zone 1, 2, 21, 22 Exd & Exe to Convert Thread Connections Between Conduit
Standard	UL1203, IECEX, ATEX, INMETRO, EACEX, CNEX
Trade Size	M50 Male to 3/4 Inch NPT Female Thread
Flexibility	None
Material	Nickel Plated Brass
Connection	Straight
Color	Metallic

### European Specifications (ETIM)

ETIM	EC000938 Enlargement/reducing ring
Thread type inner thread	NPT
Thread size inner thread (inch)	3/4 inch
Thread type outer thread	Metric
Thread size outer thread metric	50
Material	Brass
Nickel-plated	Y
Explosion-proof	Y

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	1.94 lbs. Each

### Header

3D Model	Available on Website
----------	----------------------