



Actual

Catalog Number: EXS05MLC1
Product ID: 7TCA297180R0104
UPC Number: 78621019515
EAN Number: 05011949230767
Status: Active

Double Compression Cable Gland, M25 Thread, Flameproof Ex d and Increased Safety Ex e, Suitable for use with SWA, SWB, and AWA Conduit, IP66 Rating, Inner Cable Range 12 to 20mm, Outer Cable Range 16 to 26mm, 316 Stainless Steel

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	Kopex
Type	Double Compression Gland
Application	For Use with SWA (Steel Wired Armoured), AWA (Aluminum Wired Armour), and SWB (Steel Wired Braid) Conduit to Provide Secure Cable Connections Through Knockouts and Threaded Entries
Standard	UL Listed, Approved to EN60079-0, 60079-1, 60079-7, 60079-31
Size	M25
Conductor Range	Inner 12 to 20mm, Outer 16 to 26mm
Material	Stainless Steel
Color	Metallic
Insulation	IP66 Rating
Temperature Rating	-40 to 100 Degrees C
Environmental Conditions	Flameproof Ex d and Increased Safety Ex e, Suitable for Zones 1, 2, 21, 22

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	Metric
Nominal thread size metric/PG	25
Pitch thread	1.5mm
Thread length	18mm
Hexagon angular dimension	44mm
Suitable for cable diameter	12.0-26.0mm
Material	Metal
Material quality	Stainless steel V4A
Surface protection	Untreated
Halogen free	N
Glass-fibre reinforced	N
Degree of protection (IP)	IP68
Shock resistant	N
Colour	Natural colour
Bend radius protection/trumpet flare	N
With locknut	N
Model	Straight
Flat cable coupling	N
Strain relief	N
Operating temperature	-40-+100°C
Explosion-tested version	Y
For Ex-zone gas	1, 2
For Ex-Zone dust	21, 22
EMC-version	N

Packaging

Inner Quantity	8
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	56
Outer Dimensions (inches)	11.81x11.81x7.87
Weight Uom	1.14 lbs. Each