



Actual

Catalog Number: EXS/M20/HSP
Product ID: 7TCA297140R0117
UPC Number: 78621019322
EAN Number: 05011949225848
Status: Active

Stopping Plug with Hex Head, M20 Thread, Suitable for Use in Zones 1, 2, 21, and 22, Exe I, Exe II, and Extd IIIC, IP65-66 Rating, Stainless Steel

North American Specifications (UNSPSC)

UNSPSC	39121404 Electrical sleeves
IGCC	4529 Cable end sleeve
Brand Name	Kopex
Type	Conduit Stopping Plug with Hex Head
Application	Provide Protection for the End of Conduit Systems
Standard	ATEX :- Baseefa 08ATEX0324, IECEx :- IECEx BAS08.0109
Insulation	IP65, 66
Material	Stainless Steel
Color	Metallic
Connection	Straight, Screw In
Size	M20 Thread

European Specifications (ETIM)

ETIM	EC000032 Plug for cable screw gland
Thread type	Metric
Nominal thread size metric/PG	20
Material	Metal
Material quality	Stainless steel V4A
Surface protection	Untreated
Colour	Natural colour
For Ex-zone gas	1, 2
For Ex-Zone dust	21, 22

Packaging

Inner Quantity	1
Inner Dimensions (inches)	1.4x3.2x4.5
Outer Quantity	10
Outer Dimensions (inches)	15x3x4.5
Weight Uom	11 lbs. per 100

Header

3D Model	Available on Website
----------	----------------------