



Actual

Catalog Number: FCC-2A
Product ID: 7TCG009630R0015
UPC Number: 78621096749
EAN Number: 05414363074670
Status: A

Cable Clamp for Flat Cables, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 50.7mm (2 Inches), Width of 12.7mm (0.50 Inch), Height of 8.8mm (0.35 Inch) Minimum to 30.4mm (1.2 Inches) Maximum, M4 Countersunk Screw or Self-Adhesive Mounting Method

North American Specifications (UNSPSC)

UNSPSC	39121702 Cable clips
IGCC	5029 Nylon Cable Clips
Type	Cable Clamp for Flat Cables
Cable Type	Flat
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Self-Adhesive/Screw
Number Of Cables	25

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	50.7mm
Width	12.7mm
Height	8.8mm
Type of fastening	Stick and screw
Material	Plastic
Material quality	Polyamide PA
Colour	Natural colour

Packaging

Inner Quantity	50
Outer Quantity	1000
Outer Dimensions (inches)	15x11.4x9.1
Weight Uom	2.5 lbs. per 1000