



Representative

**Catalog Number:** FO200-50-5  
**Product ID:** 7TAG009630R0029  
**UPC Number:** 78621081286  
**EAN Number:** 05414363021391  
**Status:** A

FO Slotted Loop Tie, Green Polyamide (Nylon 6.6) on Hook Side and Low Density Polyethylene on Loop Side for Temperatures up to 104.4 Degrees Celsius (220 F), Length of 228.6mm (9.0 Inches), Width of 19.05mm (0.75 Inch), Thickness of 1.588mm (0.0625 Inch), Tensile Strength Rating of 222.5 Newtons (50 Pounds)

- Enables quick and convenient bundling of data and fiber optic cables.
- Screw and adhesive mounting bases provide multiple mounting options.
- Wrap pre-determined bundle diameters using the convenient slotted head.

#### North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5047 Velcro Ties
Type	Hook and Loop
Special Features	Enables quick and convenient bundling of data and fiber optic cables.
Width	0.75 in ; 19.5 mm
Length	9 in ; 228.6 mm
Thickness	0.0625 in ; 1.588 mm
Bundle Diameter	Max 2 in ; Max 50.8 mm
Material	Polyethylene/Nylon
Color	Green
Lock Mechanism	Velcro Fastener
Tensile Strength	50 pounds ; 222 newtons

#### European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	19.05mm
Length belt/tape/tie	228.6mm
Tie thickness	1.588mm
Max. bundle diameter	50.8mm
Min. holding force	222.5N
Band closure	Velcro fastener
Material	Plastic
Material quality	Polyamide/polyethylene PA/PE
Surface protection	Untreated
Halogen free	Y
Colour	Green
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	N

#### Packaging

Inner Quantity	10
Outer Quantity	100
Weight Uom	2 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000067
--------------------------------	------------

