



Representative

Catalog Number: FO350-50-5
Product ID: 7TAG009000R0107
UPC Number: 78621081349
EAN Number: 05414363021605
Status: A

FO Slotted Loop Tie, Green Polyamide (Nylon 6.6) on Hook Side and Low Density Polyethylene on Loop Side for Temperatures up to 104.4 Degrees Celsius (220 F), Length of 330.2mm (13.0 Inches), Width of 19.05mm (0.75 Inches), Thickness of 1.588mm (0.0625 Inches), Tensile Strength Rating of 222.5 Newtons (50 Pounds)

- Enables quick and convenient bundling of data and fiber optic cables.
- Screw and adhesive mounting bases provide multiple mounting options.
- Wrap pre-determined bundle diameters using the convenient slotted head.

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5047 Velcro Ties
Type	Hook and Loop
Special Features	Enables quick and convenient bundling of data and fiber optic cables.
Width	0.75 in ; 19.05 mm
Length	13 in ; 330.2 mm
Thickness	0.063 in ; 1.6 mm
Bundle Diameter	Max 3.5 in ; Max 88.9 mm
Material	Nylon/Polyamide
Color	Green
Lock Mechanism	Velcro Fastener
Tensile Strength	50 pounds ; 220 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	19.05mm
Length belt/tape/tie	330.2mm
Tie thickness	1.588mm
Min. holding force	222.5N
Band closure	Velcro fastener
Material	Plastic
Material quality	Polyamide/polyethylene PA/PE
Surface protection	Untreated
Halogen free	Y
Colour	Green
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N

Packaging

Inner Quantity	10
Outer Quantity	100
Weight Uom	2 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000067
--------------------------------	------------

