



Actual

Catalog Number: FOR180-50-3
Product ID: 7TAG009970R0027
UPC Number: 78620998158
EAN Number: 05415022156768
Status: A

FOR Roll Hook and Loop Tie, Orange Polyethylene/Nylon for Temperatures up to 104.4 Degrees Celsius (220 F), Length of 4572.0mm (180 Inches), Width of 19.05mm (0.75 Inch), Thickness of 1.588mm (0.0625 Inch), Tensile Strength Rating of 222.5 Newtons (50 Pounds)

- Enables quick and convenient bundling of data and fiber optic cables.
- Screw and adhesive mounting bases provide multiple mounting options.
- Rolled hook and loop material enables custom cut lengths, avoiding waste.

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5047 Velcro Ties
Type	Hook and Loop
Special Features	Enables quick and convenient bundling of data and fiber optic cables.
Width	0.75 in ; 19.05 mm
Length	180 in ; 4572 mm
Material	Polyethylene/Nylon
Color	Orange
Lock Mechanism	Velcro Fastener
Tensile Strength	50 pounds ; 222 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	19.05mm
Length belt/tape/tie	4572mm
Tie thickness	1.588mm
Min. holding force	222.5N
Band closure	Velcro fastener
Material	Plastic
Material quality	Polyamide/polyethylene PA/PE
Surface protection	Untreated
Halogen free	Y
Colour	Orange
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	N

Packaging

Inner Quantity	1
Inner Dimensions (inches)	8x6x.01
Outer Quantity	10
Outer Dimensions (inches)	8x5.5x5.5
Weight Uom	13.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000067
--------------------------------	------------

