



Actual

Catalog Number: FOS320-50-0
Product ID: 7TAG009630R0048
UPC Number: 78621071227
EAN Number: 05414363022121
Status: A

FOS Strip Tie, Black Polyethylene/Nylon for Temperatures up to 104.4 Degrees Celsius (220 F), Length of 304.8mm (12.0 Inches), Width of 19.05mm (0.75 Inch), Thickness of 1.588mm (0.0625 Inch), Tensile Strength Rating of 222.5 Newtons (50 Pounds)

- Enables quick and convenient bundling of data and fiber optic cables.
- Screw and adhesive mounting bases provide multiple mounting options.
- Pre-cut lengths make bundling a cinch.

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5047 Velcro Ties
Type	Hook and Loop
Special Features	Enables quick and convenient bundling of data and fiber optic cables.
Width	0.75 in ; 19.05 mm
Length	12 in ; 304.8 mm
Thickness	0.0625 in ; 1.588 mm
Bundle Diameter	Max 3.2 in ; Max 81.28 mm
Material	Polyethylene/Nylon
Color	Black
Lock Mechanism	Velcro Fastener
Tensile Strength	50 pounds ; 222 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	19.05mm
Length belt/tape/tie	304.8mm
Tie thickness	1.588mm
Max. bundle diameter	81.3mm
Min. holding force	222.5N
Operating temperature	-20-104.4°C
Band closure	Velcro fastener
Material	Plastic
Material quality	Polyamide/polyethylene PA/PE
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	N

Packaging

Inner Quantity	10
Outer Quantity	100
Weight Uom	8.13 lbs. per 1000



Documents / Support Tools

Technical Drawing / Data Sheet

WSD-000067