



Representative

**Catalog Number:** H050BHD  
**Product ID:** 7TBD013070R0000  
**UPC Number:** 78621000242  
**EAN Number:** 05415022173291  
**Status:** A

1/2 Inch Zinc Bulkhead Fittings with Thermoplastic Insulating Throat, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

- For use with rigid/IMC conduit

#### North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Type	Bulkhead Fitting
Special Features	Thermoplastic Insulating Throat with Rating up to 105 Degree Celsius
Application	A Fitting for Connecting a Junction Box to a Conduit System
Standard	UL E23018, CSA
Trade Size	1/2 in
Outside Diameter	1-7/16 in
Material	Zinc

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Connection type screw connection to housing	Thread
Thread type	NPT
Material housing	Zinc die-cast
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y
Operating temperature	0-+105°C

#### Packaging

Inner Quantity	20
Inner Dimensions (inches)	6.1x5x4
Outer Quantity	40
Outer Dimensions (inches)	10.6x6.3x4.6
Weight Uom	30.38 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

#### Header

3D Model	Available on Website
----------	----------------------

