



Representative

Catalog Number: H050CAPA
Product ID: 7TBD013430R0001
UPC Number: 78621004893
EAN Number: 05415022434996
Status: A

1/2 Inch Aluminum, Capoff with Thermoplastic Insulating Throat, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

- CSA Certified for hazardous locations Class II Groups E.F.G. Class III
- Meets NEMA sealing requirements for NEMA 3R, 4 & 13 enclosures.

North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Type	Hubs & Accessories
Special Features	Insulating Throat with a Thermoplastic Temperature Rating of 105 Degrees Celsius
Application	For Use with Rigid/IMC Conduit
Standard	UL E23018, CSA
Trade Size	1/2 in
Outside Diameter	1-7/16 in
Length	1-13/32 in
Material	Aluminum

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Connection type screw connection to housing	Thread
Thread type	NPT
Material housing	Other
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y
Operating temperature	0-+105°C

Packaging

Inner Quantity	25
Outer Quantity	100
Outer Dimensions (inches)	10.7x9.6x3.4
Weight Uom	5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website