



Representative

**Catalog Number:** H050CP  
**Product ID:** 7TBD013790R0000  
**UPC Number:** 78621000187  
**EAN Number:** 05414363152279  
**Status:** A

1/2 Inch Zinc Hub Connector with Chrome Plating, Thermoplastic Insulating Throat, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Type	Hub Connector
Special Features	Sealing Ring and Groove with Innovative Profile Better Than Standard O-Ring
Application	To Connect Threaded Metal Conduit to a Threadless Opening in a Box or Enclosure
Standard	UL E23018, CSA
Size	1/2 Inch
Material	Zinc
Finish	Chrome Plating
Temperature Rating	105 C

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Connection type screw connection to housing	Thread
Thread type	NPT
Material housing	Zinc die-cast

### Packaging

Inner Quantity	25
Outer Quantity	100
Outer Dimensions (inches)	12.6x8.6x4.5
Weight Uom	21.5 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website