



Representative

**Catalog Number:** H075A  
**Product ID:** 7TBD013780R0002  
**UPC Number:** 78621089842  
**EAN Number:** 05415022257809  
**Status:** A

3/4 Inch Aluminum, Hub Connector with Thermoplastic Insulating Throat, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

#### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Type	Hub Connector
Special Features	Sealing Ring and Groove with Innovative Profile Better Than Standard O-Ring
Application	To Connect Threaded Metal Conduit to a Threadless Opening in a Box or Enclosure
Standard	UL E23018, CSA
Size	3/4 Inch
Material	Aluminum
Temperature Rating	105 C

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/4 inch
Model	Straight
Revolving thread	N
Connection type screw connection to housing	Thread
Thread type	NPT
Material housing	Other

#### Packaging

Inner Quantity	25
Outer Quantity	100
Outer Dimensions (inches)	17x10.5x4.5
Weight Uom	11.5 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------