



Representative

**Catalog Number:** H075BHD  
**Product ID:** 7TBD013070R0002  
**UPC Number:** 78621000243  
**EAN Number:** 05415022258066  
**Status:** A

3/4 Inch Zinc Bulkhead Fittings with Thermoplastic Insulating Throat, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

- For use with rigid/IMC conduit

**North American Specifications (UNSPSC)**

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Type	Bulkhead Fitting
Special Features	Thermoplastic Insulating Throat with Rating up to 105 Degree Celsius
Application	A Fitting for Connecting a Junction Box to a Conduit System
Standard	UL E23018, CSA
Trade Size	3/4 in
Outside Diameter	1-11/16 in
Material	Zinc

**European Specifications (ETIM)**

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/4 inch
Model	Straight
Revolving thread	N
Connection type screw connection to housing	Thread
Thread type	NPT
Material housing	Zinc die-cast
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y
Operating temperature	0-+105°C

**Packaging**

Inner Quantity	20
Outer Quantity	40
Outer Dimensions (inches)	10.6x8.4x4.7
Weight Uom	0.5 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

**Header**

3D Model	Available on Website
----------	----------------------