



Representative

**Catalog Number:** H075CAPA  
**Product ID:** 7TBD013430R0004  
**UPC Number:** 78621004894  
**EAN Number:** 05415022435009  
**Status:** A

3/4 Inch Aluminum, Capoff with Thermoplastic Insulating Throat, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

- CSA Certified for hazardous locations Class II Groups E.F.G. Class III
- Meets NEMA sealing requirements for NEMA 3R, 4 & 13 enclosures.

**North American Specifications (UNSPSC)**

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Type	Hubs & Accessories
Special Features	Insulating Throat with a Thermoplastic Temperature Rating of 105 Degrees Celsius
Application	For Use with Rigid/IMC Conduit
Standard	UL E23018, CSA
Trade Size	3/4 in
Outside Diameter	1-11/16 in
Length	1-15/32 in
Material	Aluminum

**European Specifications (ETIM)**

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/4 inch
Model	Straight
Revolving thread	N
Connection type screw connection to housing	Thread
Thread type	NPT
Material housing	Other
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y
Operating temperature	0-+105°C

**Packaging**

Inner Quantity	25
Inner Dimensions (inches)	11.6x4.3x3.5
Outer Quantity	50
Weight Uom	7 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------