




Actual



Representative

**Catalog Number:** H075GRSST  
**Product ID:** 7TBD013740R0001  
**UPC Number:** 78621000278  
**EAN Number:** 05415022257007  
**Status:** A

3/4 Inch 316 Stainless Steel Grounding Hub, Thermoplastic Insulating Throat, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

- Suitable for hazardous locations use in Class I, Division 2; Class II, Division 1&2; Class III, Division 1 & 2 per NEC 501-4(b); 502-4 (a) and 503-3 (a)
- Suitable for hazardous locations use in Class II, Groups E, F, G & Class III locations per CEC 18-202; 18-252; 18-302; 18-352.
- Meets NEMA sealing requirements for NEMA 3R, 4, 4X and 13 enclosures

**North American Specifications (UNSPSC)**

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Type	Grounding Hub
Special Features	Hexagonal/Splined Body and Locknut Enable Fast and Easy Installation
Application	For Use with Rigid/IMC Conduit
Standard	UL E23018, CSA
Trade Size	3/4 in
Outside Diameter	1.44 in
Length	1.59 in
Material	316 Stainless Steel

**European Specifications (ETIM)**

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/4 inch
Model	Straight
Revolving thread	N
Connection type screw connection to housing	Thread
Thread type	NPT
Material housing	Stainless steel

**Packaging**

Inner Quantity	25
Inner Dimensions (inches)	8x5x4
Outer Quantity	100
Outer Dimensions (inches)	16.6x10.5x4.5
Weight Uom	35 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------