



Representative

Catalog Number: H100A
Product ID: 7TBD013780R0005
UPC Number: 78621089843
EAN Number: 05415022259995
Status: A

1 Inch Aluminum, Hub Connector with Thermoplastic Insulating Throat, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Type	Hub Connector
Special Features	Sealing Ring and Groove with Innovative Profile Better Than Standard O-Ring
Application	To Connect Threaded Metal Conduit to a Threadless Opening in a Box or Enclosure
Standard	UL E23018, CSA
Size	1 Inch
Material	Aluminum
Temperature Rating	105 C

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 inch
Model	Straight
Revolving thread	N
Connection type screw connection to housing	Thread
Thread type	NPT
Material housing	Other

Packaging

Inner Quantity	5
Inner Dimensions (inches)	5.2x4.6x3.4
Outer Quantity	25
Outer Dimensions (inches)	24x5.5x4
Weight Uom	19 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website