



Representative

**Catalog Number:** H125A  
**Product ID:** 7TBD013790R0007  
**UPC Number:** 78621090346  
**EAN Number:** 05415022258349  
**Status:** A

1-1/4 Inch Aluminum, Hub Connector with Thermoplastic Insulating Throat, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Type	Hub Connector
Special Features	Sealing Ring and Groove with Innovative Profile Better Than Standard O-Ring
Application	To Connect Threaded Metal Conduit to a Threadless Opening in a Box or Enclosure
Standard	UL E23018, CSA
Size	1-1/4 Inch
Material	Aluminum
Temperature Rating	105 C

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/4 inch
Model	Straight
Revolving thread	N
Connection type screw connection to housing	Thread
Thread type	NPT
Material housing	Other

### Packaging

Inner Quantity	5
Outer Quantity	15
Outer Dimensions (inches)	10.9x6.55x5.34
Weight Uom	25 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website