



Representative

Catalog Number: H125BHDA
Product ID: 7TBD013080R0011
UPC Number: 78621000332
Status: A

1-1/4 Inch Aluminum, Bulkhead Fittings with Insulating Throat Thermoplastic, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

North American Specifications (UNSPSC)

| | |
|------------------|--|
| UNSPSC | 39131707 Electrical conduit coupling |
| IGCC | 5548 Electrical conduit coupling |
| Type | Bulkhead Fitting |
| Special Features | Thermoplastic Insulating Throat with Rating up to 105 Degree Celsius |
| Application | A Fitting for Connecting a Junction Box to a Conduit System |
| Standard | UL E23018, CSA |
| Trade Size | 1-1/4 in |
| Outside Diameter | 2-3/8 in |
| Material | Aluminum |

European Specifications (ETIM)

| | |
|---|--|
| ETIM | EC001180 Screw connection for protective metallic hose |
| Nominal size in inch | 1 1/4 inch |
| Model | Straight |
| Revolving thread | N |
| Connection type screw connection to housing | Thread |
| Thread type | NPT |
| Material housing | Other |
| Approved in combination with protective conduit CSA | Y |
| Approved in combination with protective conduit UL | Y |
| Operating temperature | 0-+105°C |

Packaging

| | |
|---------------------------|-----------------|
| Inner Quantity | 5 |
| Outer Quantity | 10 |
| Outer Dimensions (inches) | xx |
| Weight Uom | 40 lbs. per 100 |

Documents / Support Tools

| | |
|-----------------------------------|----------------------|
| Technical Drawing / Data Sheet US | Available on Website |
|-----------------------------------|----------------------|