



Representative

**Catalog Number:** H125CP  
**Product ID:** 7TBD013800R0013  
**UPC Number:** 78621000190  
**EAN Number:** 05415022243451  
**Status:** A

1-1/4 Inch Zinc Hub Connector with Chrome Plating, Thermoplastic Insulating Throat, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Type	Hub Connector
Special Features	Sealing Ring and Groove with Innovative Profile Better Than Standard O-Ring
Application	To Connect Threaded Metal Conduit to a Threadless Opening in a Box or Enclosure
Standard	UL E23018, CSA
Size	1-1/4 Inch
Material	Zinc
Finish	Chrome Plating
Temperature Rating	105 C

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/4 inch
Model	Straight
Revolving thread	N
Connection type screw connection to housing	Thread
Thread type	NPT
Material housing	Zinc die-cast

### Packaging

Inner Quantity	5
Outer Quantity	15
Outer Dimensions (inches)	11.125x6.625x5.25
Weight Uom	43.75 lbs. per 100

### Documents / Support Tools

Catalog Page	Available on Website
--------------	----------------------